

<p>NEW TUBE RELEASES for use with TRC 2-1-70 DATA BOOK</p>
--

TUBE	SECT	A	B	C	D	CATH	CONT	TEST
3DJ3		2	5	27	4	-	12357	0
4GS7	Tri	4	6	21	2	38	38	12
"	Pen	4	6	19	2	-	-	679
4MK8	Pen-1	4	6	22	2	1	-	237
"	Pen-2	4	6	22	2	-	-	278
6AQ8	Tri-1	4	9	22	2	8	-	67
"	Tri-2	4	9	22	2	3	-	12
6BW3								
Key at 0		1	9	17	3	7	-	4
6DS5		3	9	25	2	2	17	●1756
	●Ignore glow on 1							
6HL7		6	9	20	2	1	3459	●39278
	●Ignore glow on 3							
6RA6		5	9	17	3	1	27	29
	Must show short on 2-7							
	Grid short test - Throw 2-7 together							
8LX8	Tri	4	10	22	2	8	-	19
"	Pen	4	10	21	2	7	-	236
8MD8	Tri-1	4	10	22	2	7	-	36
"	Tri-2	4	10	22	2	-	-	28
"	Tri-3	4	10	22	2	-	-	19
9RA6		5	11	17	3	1	27	29
	Must show short on 2-7							
	Grid short test - Throw 2-7 together							
10LM8	Tri	4	12	23	2	8	-	19
"	Pen	4	12	23	2	7	-	236
10LY8	Tri	4	12	22	2	1	-	23
"	Pen	4	12	20	2	6	-	789
10T10								
Key at 6	Pen-1	5	12	19	3	2	-	134
Key at 2	Pen-2	1	12	19	3	4	-	5789
12CT3		4	13	23	2	9	26	●26
	●Ignore glow on 2							
12DZ7	Pen-1	2	13	5	1	8	-	456
"	Pen-2	2	13	5	1	-	-	134
12HB25*		4	13	21	2	9	123678	●12670
	●Ignore glow on 1-6 - Cap goes to top of tube							
	*Must use magnoval adapter							
12HU8	Pen-1	4	13	22	2	7	-	123
"	Pen-2	4	13	22	2	-	-	689

(OVER)

TUBE	SECT	A	B	C	D	CATH	CONT	TEST
17JF6		4	15	20	2	3	1267	●12670
	●Ignore glow on 1-2-6 - Cap goes to top of tube							
17Y9	Pen-1	5	15	20	2	7	-	890
"	Pen-2	5	15	20	2	2	-	134
19FX5		3	16	17	3	1	25	267
	Lever #5 must be thrown to open position							
22KV6		4	17	20	2	3	17	279
	Lever #1 must be thrown to open position							
25BB14*		4	18	20	2	38	123678	●12670
	●Ignore glow on 1-6 - Cap goes to top of tube							
	*Must use magnoval adapter							
26HV5								
Key at 0		1	18	20	2	4	-	27
30JZ6								
Key at 3		2	19	20	2	5	-	780
	Cap goes to top of tube							
31LQ6		4	19	23	2	3	1267	●126780
	●Ignore glow on 1-2 - Cap goes to top of tube							
40KG6*		4	19	20	2	9	123678	680
	Levers #1-2-3 must be thrown to open position							
	Cap goes to top of tube							
	*Must use magnoval adapter							
42EC4*		4	19	22	2	0	278	●278
	●Ignore glow on 2-7 - Cap goes to top of tube							
	*Must use magnoval adapter							

### FOREIGN

E-810F		4	9	19	2	13	1369	2679
EF-804		4	9	23	2	3	26	789
PCC-85	Tri-1	4	11	22	2	8	-	67
"	Tri-2	4	11	22	2	3	-	12
PY-500*		4	19	22	2	0	278	●278
	●Ignore glow on 2-7 - Cap goes to top of tube							
	*Must use magnoval adapter							
UCC-85	Tri-1	4	18	22	2	8	-	67
"	Tri-2	4	18	22	2	3	-	12